

The Stratasys F123 Series

The Stratasys [F120™, F170™, F270™ and F370™ 3D printers](#) combine dependable [FDM® technology](#) with design-to-print [GrabCAD Print™ software](#) for accurate, professional 3D printing results. ProtectAM™ technology on the F370 provides print data security that includes U.S. Department of Defense STIG compliance.

F123 Series printers are designed for ease of use, so you don't need special 3D printing expertise. True plug-and-play capability, auto-calibration and fast, easy material swaps mean more time printing, maximizing your productivity. Super-quiet, clean operation makes any of these printers right at home in an office or classroom environment.

Fast-draft mode prints initial design concepts quickly and economically, while consuming half the material on average. Hands-free soluble support removal enables the creation of complex parts without compromising accuracy or detail. Remote monitoring lets you easily manage your print jobs from outside the office.

Product Specifications

System Size and Weight	F120: 889 x 870 x 721 mm (35 x 35 x 29 in.), 124 kg (275 lbs) F170, F270, F370: 1,626 x 864 x 711 mm (64 x 34 x 28 in.), 227 kg (500 lbs) with consumables
Noise Specification	46 dB maximum during build, 35 dB when idle
Accuracy ¹	Parts are produced within an accuracy of +/- .200 mm (.008 in), or +/- .002 mm/mm (.002 in/in), whichever is greater.
Material Delivery Options	Stratasys F120: 2 material coil boxes, 1 for model, 1 for support located external to printer Stratasys F170: 2 material spool bays, 1 for model, 1 for support located in a drawer on the front of the unit Stratasys F270/F370: 4 material spool bays, 2 for model, 2 for support located in a drawer on the front of the unit
Network Connectivity	Wired: TCP/IP protocols at 100 Mbps minimum 100 base T, Ethernet protocol, RJ45 connector Wireless-ready: IEEE 802.11n, g, or b; Authentication: WPA2-PSK, 802.1x EAP Encryption: CCMP, TKIP
Software	GrabCAD Print (download): Stratasys F120, F170, F270 and F370 Insight software license: Stratasys F370 only DOD STIG Compliance powered by Red Hat® Enterprise Linux® software: Stratasys F370 only
System Requirements	Windows 7, 8, 8.1 and 10 (64bit only) with a minimum of 4GB RAM (8GB or more recommended)
Operating Environment	Operating: Temperature: 15 – 30 °C (59 – 86 °F), Humidity: 30 – 70% RH Storage: Temperature: 0 – 35 °C (32 – 95 °F), Humidity: 20 – 90% RH
Power Requirements	100–132V/15A or 200–240V/7A. 50/60 Hz
Regulatory Compliance	CE (low-voltage and EMC directive), FCC, EAC, cTUVus, FCC, KC, RoHs, WEEE, Reach, RCM

The Stratasys F123 Series

Model Capabilities

Printer	Maximum Build Size (XYZ)	Model Materials
Stratasys F120	254 x 254 x 254 mm (10 x 10 x 10 in.)	ABS-M30™, ASA, SR-30 Support material
Stratasys F170	254 x 254 x 254 mm (10 x 10 x 10 in.)	PLA ² , ABS-M30, ASA, FDM TPU 92A, ABS-CF10, QSR™ Support material
Stratasys F270	305 x 254 x 305 mm (12 x 10 x 12 in.)	PLA ² , ABS-M30, ASA, FDM TPU 92A, ABS-CF10, QSR Support material
Stratasys F370	355 x 254 x 355 mm (14 x 10 x 14 in.)	PLA ² , ABS-ESD7™, ABS-M30, ASA, Diran™ 410MF07 ² , FDM TPU 92A, PC-ABS, ABS-CF10, QSR Support material

Layer Thickness

Material	0.013 in. (0.330 mm)	0.010 in. (0.254 mm)	0.007 in. (0.178 mm)	0.005 in. (0.127 mm) ³
PLA	○	●	○	○
ABS	●	●	●	●
ASA	●	●	●	●
PC-ABS	●	●	●	●
ABS-ESD7	○	●	○	○
Diran 410MF07	●	●	●	○
FDM TPU 92A	○	●	○	○
ABS-CF10³	●	●	●	○

¹ Accuracy is geometry-dependent. Achievable accuracy specification derived from statistical data at 95% dimensional yield. Z part accuracy includes an additional tolerance of -0.000/+slice height.

² PLA and Diran 410MF07 do not utilize soluble support material. The supports are made of breakaway PLA.

³ Not available on the F120.

Stratasys Headquarters

7665 Commerce Way,
Eden Prairie, MN 55344
+1 800 801 6491 (US Toll Free)
+1 952 937-3000 (Intl)
+1 952 937-0070 (Fax)

1 Holtzman St., Science Park,
PO Box 2496
Rehovot 76124, Israel
+972 74 745 4000
+972 74 745 5000 (Fax)

stratasys.com

ISO 9001:2008 Certified

© 2021 Stratasys. All rights reserved. Stratasys, Stratasys signet and FDM are registered trademarks of Stratasys Inc. F123, F120, F170, F270, F370, ABS-M30, ABS-ESD7, Diran 410MF07, ABS-CF10, QSR Support, GrabCAD Print and ProtectAM are trademarks of Stratasys, Inc. Red Hat is a registered trademark of Red Hat, Inc. in the United States and other countries. All other trademarks are the property of their respective owners and Stratasys assumes no responsibility with regard to the selection, performance, or use of these non-Stratasys products. Product specifications subject to change without notice. PSS_FDM_F123Series_0721a

